

Use of Indalloy® low temperature alloys for lens blocking

APPLICATION NOTE

Lens blocking alloys are used to attach optical lens blanks to surfacing blocks for grinding the required optical prescription into the lens blank.

The advantage of using low melting temperature alloys is that they conform to any lens configuration, are easy to use, and recyclable.

Plastic lenses: The low melting temperature alloy used for plastic lenses is Indalloy® 117, with a melting temperature of 117°F. Due to the popularity of plastic lens, it is the most common alloy for lens blocking and can also be used for glass lenses. This is because plastic lenses will warp if a higher temperature alloy is used. In many facilities Indalloy 117 is used exclusively to prevent the accidental use of a higher temperature alloy on plastic lenses.

Glass lenses: In addition to Indalloy 117, Indalloy 158, with a melting temperature of 158°F, is another commonly used alloy. However, Indalloy 158 has a better bond strength and is used only for glass lenses.

Two other alloys that can be used for glass lenses are Indalloy 19 and 136. Indalloy 19 has a melting point of 140° F and is both lead and cadmium free. Indalloy 136 has a melting point of 136°F and is cadmium free. These offer the advantage of reduced environmental and health concerns, but compared to Indalloy 158 have reduced bond strengths. Also, their higher temperatures are prohibitive for use with plastic lenses.

Lens blocking: A protective plastic tape is placed over the lens blank prior to mounting the lens blank and surfacing block into the blocker. The blocker contains the molten alloy (approximately 5°F above the liquidus temperature of the alloy) until it is forced, by air pressure or manual hand pump, between the tape on the lens blank and surfacing block. The alloy is cooled until it solidifies and bonds the lens blank tape to the surfacing block.

The surfacing block is then mounted in a chuck and is used to protect the lens during the grinding operation. After the grinding operation, plastic lenses are removed from the surfacing block by the inertia of knocking the surfacing block on a solid surface. Glass lenses are removed by dipping them into a hot water bath. When the alloy melts and the lens is separated from the surfacing block, the alloy settles to the bottom and is recovered by draining it through a valve.



Indalloy No.	Composition	Liquidus°F	Solidus°F
117	44.7Bi 22.6Pb 19.1In 8.3Sn 5.3Cd	117	117
136	49Bi 21In 18Pb 12Sn	136	136
19	51In 32.5Bi 16.5Sn	140	140
158	50Bi 26.7Pb 13.3Sn 10Cd	158	158

This product data sheet is provided for general information only. It is not intended, and shall not be construed, to warrant or guarantee the performance of the products described which are sold subject exclusively to written warranties and limitations thereon included in product packaging and invoices.

Form No. 97612 R3

S O L D E R

INDIUM CORPORATION®

www.indium.com
 askus@indium.com
 PRC +86 (0)512 628 34900
 SINGAPORE +65 6268 8678
 UK +44 (0) 1908 580400
 USA +1 315 853 4900

